

Product leaflet

Product	Model No.	Ordering No.
Gas filter ABE1	SR 315	H02-3212
Gas filter ABE2	SR 294	H02-3312

Product Description

Gas filter SR 315, Class 1, and SR 294, Class 2, are designed for use with Sundström half masks and full face masks. Both filters are of type ABE and provide protection against the following types of gases and vapours:

Type A protects against organic gases and vapours, such as solvents, with boiling points > +65 °C.

Type B protects against inorganic gases and vapours, such as chlorine, hydrogen sulphide and hydrogen cyanide.


Type E protects against acidic gases and vapours, such as sulphur dioxide and hydrogen fluoride.

The gas filters can easily be combined with particle filter SR 510 P3 in order to obtain protection also against aerosols (particles), e.g. during spray painting.

Technical specification

	SR 315 ABE1	EN 14387:2004	SR 294 ABE2	EN 14387:2004
Pressure drop at 30 l/min	≈ 55 Pa	≤ 100 Pa	≈ 95 Pa	≤ 140 Pa
Diameter/height	106/28 mm	-	106/48 mm	-
Weight	≈ 125 g	≤ 300 g	≈ 230 g	≤ 300 g
Service temperature	-10 – +55 °C, < 90 % RH	-	-10 – +55 °C, < 90 % RH	-
Storage temperature	-20 – +40 °C, < 90 % RH	-	-20 – +40 °C, < 90 % RH	-
Resistance time				
A1, Cyclohexane C₆H₁₂, 1,000 ppm	> 95 min	≥ 70 min	-	-
B1, Chlorine Cl₂, 1,000 ppm	> 30 min	≥ 20 min	-	-
B1, Hydrogen Sulphide H₂S, 1,000 ppm	> 60 min	≥ 40 min	-	-
B1, Hydrogen Cyanide HCN, 1,000 ppm	> 40 min	≥ 25 min	-	-
E1, Sulphur Dioxide SO₂, 1,000 ppm	> 30 min	≥ 20 min	-	-
A2, Cyclohexane C₆H₁₂, 5,000 ppm	-	-	> 40 min	≥ 35 min
B2, Chlorine Cl₂, 5,000 ppm	-	-	> 30 min	≥ 20 min
B2, Hydrogen Sulphide H₂S, 5,000 ppm	-	-	> 60 min	≥ 40 min
B2, Hydrogen Cyanide HCN, 5,000 ppm	-	-	> 35 min	≥ 25 min
E2, Sulphur Dioxide SO₂, 5,000 ppm	-	-	> 30 min	≥ 20 min
Approval	EN 14387:2004		EN 14387:2004	

- A. Activated carbon**
- B. Filter disc**
- C. Marking label**
- D. Filter case**



Head Office

Tel: +46-(0)8-562 370 00
 Fax: +46-(0)8-562 370 20
 P.O. Box 10056
 SE-181 10 Lidingö
 Sweden
 Visiting address:
 Vasavägen 84
 SE-181 10 Lidingö

Factory

Tel: +46-(0)8-562 370 00
 Fax: +46-(0)8-562 370 60
 P.O. Box 76
 SE-340 14 Lagan
 Sweden
 Visiting address:
 Västergatan 4
 SE-340 14 Lagan